

48-Device USB Charging Station Cabinet with Sync for iPad and Android Tablets, Wall-Mount and Cart Options, Black

MODEL NUMBER: **CS48USB**



Description

The CS48USB 48-Device USB Charging Station Cabinet provides fast charging, convenient syncing, secure storage and cord management for up to 48 iPad, Android, Surface and Kindle tablets, as well as mobile phones and other USB devices. It's recommended for education, office, commercial, retail, industrial and healthcare environments.

48 USB ports deliver the fastest charging supported by each device, up to 2.4A per port. The charging station also supports wired and wireless syncing, including syncing while charging.

The steel cabinet promotes comprehensive device protection with steel construction and a black powder-coated finish for long-term durability. It locks with the included keys to help prevent device theft, damage or tampering. Flow-through ventilation protects against overheating, and the coated shelves help prevent scratches and scuffs. The charging station also provides clutter-free organization of devices and cabling.

The CS48USB is easy to configure. It ships fully assembled and supports mounting to a wall, desk, table, counter or floor. The front door opens 180 degrees for improved device and service access, and removable dividers accommodate thicker devices. You can convert the CS48USB to a mobile cart with Tripp Lite's optional [CSHANDLEKIT](#) accessory (sold separately).

Features

Fast Charging

- 48 USB ports provide fastest charging supported by each device, up to 2.4A per port
- Recommended for iPad®, Android™, Surface™ and Kindle™ tablets
- Also charges mobile phones and other USB devices

Highlights

- Fast 2.4A USB charging, syncing and storage for 48 devices
- Locking steel cabinet with flow-through ventilation
- Adjustable device dividers and integrated cord management
- Ships fully assembled and mounts to wall, desk, table or floor
- Detachable 10 ft. power cord

Package Includes

- CS48USB 48-Device USB Charging Station Cabinet, Black
- Detachable 10 ft. AC input cord w/NEMA 5-15P plug
- (2) Keys
- Owner's manual



- Detachable 10 ft. AC input cord with NEMA 5-15P plug

Convenient Syncing

- USB sync uplink port connects to host computer for wired syncing
- Compatible with wireless syncing
- Supports simultaneous syncing and charging (up to 1.5A per port during wired syncing)

Comprehensive Protection

- Sturdy steel construction and powder-coated finish promote long-term durability
- Doors lock with included keys to help prevent device theft, damage or tampering
- Flow-through ventilation helps prevent devices from overheating
- Coated shelves shield devices from scratches and scuffs

Flexible Configuration

- Ships fully assembled
- Supports mounting to wall, desk, table, counter or floor
- Door opens 180 degrees for improved device and service access
- Removable dividers accommodate thicker devices
- Firmware upgrade port for future updates
- Converts to mobile cart with optional [CSHANDLEKIT](#) accessory (sold separately)

Specifications

MODEL TEXT	
Key Benefit	Locking steel cabinet provides 2.4A USB charging, syncing, secure storage and cord management for up to 48 tablets and other USB devices. Recommended for education, office, commercial, retail, industrial and healthcare environments.
OUTPUT	
Charging Ports / Amps	(48) 2.4A
Charging Method	USB
INPUT	
Input Connection Type	C14 inlet with 100-250V AC compatibility. Also accepts user-supplied country-specific AC cordsets
Voltage Compatibility (VAC)	110-240
Input Frequency	50 / 60 Hz (auto-select)
PHYSICAL	
Shipping Dimensions (hwd / in.)	41 x 28.4 x 26.4



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	104.1 x 72.1 x 67.1
Shipping Weight (lbs.)	183
Shipping Weight (kg)	82.4
Unit Dimensions (hwd / in.)	35.6 x 23.62 x 21.6
Unit Dimensions (hwd / cm)	90.42 x 59.9 x 54.86
Unit Weight (lbs.)	150
Unit Weight (kg)	68.04
Color	Black
Slot Dimensions - Top (hwd / in.)	8.1 x 0.8 x 13.9
Slot Dimensions - Top (hwd / mm)	206 x 20.1 x 353.8
Slot Dimensions - Bottom (hwd / in.)	8.0 x 0.8 x 13.9
Slot Dimensions - Bottom (hwd / mm)	204 x 20.1 x 353.8
Slot Dimensions - Middle (hwd / in.)	8.0 x 0.8 x 13.9
Slot Dimensions - Middle (hwd / mm)	204 x 20.1 x 353.8
Charging Station Form Factor	Stationary Cabinet
CERTIFICATIONS	
Certifications	Tested to EIA-310-E, UL60950, FCC & IEC Class B
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>