

## External 240V Tower Battery Pack for select Tripp Lite UPS Systems (BP240V400)

MODEL NUMBER: **BP240V400**



### Highlights

- Extends runtime of compatible Tripp Lite UPS Systems using 240VDC configuration
- Internal DC disconnect
- 10 year design lifespan
- Hardwire installation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Description

Tripp Lite's BP240V400 External Battery Pack offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Requires BP240EXTNDR15A to connect to UPS. Cabling for additional battery packs is contractor supplied.

COMPATIBLE UPS SYSTEMS: [SU20K3/3](#), [SU30K3/3](#) and other Tripp Lite UPS systems specifying the use of this battery pack

### Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Multiple battery packs can be daisy-chained through each other to the UPS for even longer extended run operation
- Internal DC disconnect
- 10 year design lifespan

## Specifications

BATTERY	
Expandable Battery Runtime	Multiple battery packs can be daisy-chained to the UPS for extended runtime
DC System Voltage (VDC)	240
UPS Connection	Requires BP240EXTNDR15A to connect to UPS
Expandable Runtime	Yes



<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	66 x 46 x 48
Shipping Dimensions (hwd / cm)	168 x 117 x 122
Shipping Weight (lbs.)	2200
Shipping Weight (kg)	998.8
Unit Dimensions (hwd / in.)	59 x 29 x 31.5
Unit Dimensions (hwd / cm)	149.9 x 73.7 x 80
Unit Weight (lbs.)	2020
Unit Weight (kg)	917.1
Material of Construction	Steel
Unit Weight Details	Floor loading of 288 lbs per sq. ft. / 1410 kg per sq. meter
External Battery Pack Form Factor	Tower
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104F; (0 to 40C)
Storage Temperature Range	5 to 104F; (-15 to 40C)
Relative Humidity	5 to 95% (non-condensing)
Operating Elevation (ft.)	0 to 10,000
Operating Elevation (m)	0 to 3000
<b>CERTIFICATIONS</b>	
UPS Certifications	CE; Tested to CSA (Canada); Tested to UL1778 (USA)
UPS Certification Details	EN 62040-1-2:2003, EN 60950-1, CSA C22.2 NO. 107.1
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>