

Portable 10,400mAh Dual-Port Mobile Power Bank USB Battery Charger with Auto-Sensing Charging Port

MODEL NUMBER: **UPB-10K4-S2U**



Compact 2-port 10,400mAh power bank charges multiple smartphones, tablets, e-readers, MP3 players and other handheld mobile devices anywhere, anytime, without plugging into an AC power outlet.

Description

No more frantic searching for an AC power outlet when your mobile device's battery power is getting low. The high-capacity UPB-10K4-S2U 10,400mAh Dual-Port Mobile Power Bank is an ideal power solution when you're on the road or stuck somewhere without convenient electricity. The portable dual-USB battery charger weighs barely half a pound, and fits comfortably in your purse or backpack to keep your phone, tablet, e-reader, MP3 player, digital camera or other handheld device operating when you need it.

Just connect your devices to the UPB-10K4-S2U's USB-A ports using the included USB Micro-B cable and/or another cable suitable for your device. The devices will begin charging immediately. Press the on/off button to monitor the power bank's battery capacity via the easy-to-read LEDs and know how much charge is available.

The dual USB ports provide up to 5V 1A and 5V 2.4A of power, respectively, so you can charge two devices at once. In addition, the 2.4A port benefits from auto-sensing technology that identifies how much amperage the connected device is designed to take and adjusts its charging accordingly.

The lithium-ion battery's hearty 10,400mAh capacity charges devices at maximum power draw for hours. It protects against short circuits, overvoltage, overcurrent, overcharges and overdischarges for safe, reliable charging. To charge the UPB-10K4-S2U, connect the USB Micro-B port to a USB charger or a computer's USB port using the included cable.

Features

Travel-Sized for Convenient Charging of Dual Devices Anywhere

Highlights

- Dual USB-A ports provide up to 5V 1A and 5V 2.4A of power
- Auto-sensing port adjusts amperage to match connected device
- LEDs indicate remaining battery capacity at a glance
- 3 ft. USB Micro-B charging cable included
- Compact form fits comfortably in your purse or backpack

Package Includes

- UPB-10K4-S2U 10,400mAh Dual-Port Mobile Power Bank USB Battery Charger
- USB Micro-B cable, 3 ft.
- Owner's manual



- Compact form fits comfortably in your purse or backpack
- Ideal for charging up to 2 smartphones, tablets, e-readers, MP3 players and other handheld mobile devices simultaneously
- Works with Android, Apple and Windows devices

Built-In 10,400mAh Lithium-Ion Battery Charges Without an AC Power Outlet

- Charges at maximum power draw for hours to ensure your devices are ready when you need them
- Dual USB ports provide up to 5V 1A and 5V 2.4A of power
- Auto-sensing 2.4A port adjusts amperage to match amperage of connected device
- Protects against short circuits, overvoltage, overcurrent, overcharges and overdischarges

Easy to Recharge for the Next Time You Leave Home or Office

- USB Micro-B port connects to USB charger or computer's USB-A port to charge internal battery
- Built-in LEDs indicate at a glance how much battery capacity is left
- 3 ft. USB Micro-B charging cable included

Specifications

OVERVIEW	
UPC Code	037332203922
Over Current Protection	Yes
Technology	USB
OUTPUT	
Charging Ports / Amps	(1) 1A; (1) 2.4A
Charging Method	USB
PHYSICAL	
Shipping Dimensions (hwd / in.)	1.81 x 9.25 x 4.65
Shipping Dimensions (hwd / cm)	4.60 x 23.50 x 11.81
Shipping Weight (lbs.)	0.29
Shipping Weight (kg)	0.13
Unit Dimensions (hwd / in.)	5.5 x 2.5 x 1
Unit Dimensions (hwd / cm)	14 x 6.4 x 2.5
Unit Weight (lbs.)	0.6
Unit Weight (kg)	0.27
Material of Construction	ABS



Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	5 to 113 F (-15 to 45 C)
Relative Humidity	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MICRO-USB B (FEMALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>