

Cat6 Straight-Through Modular Compact In-Line Coupler (RJ45 F/F), White, TAA

MODEL NUMBER: N234-001-WH



Connects two Cat6 cables to create one longer cable. Provides feed-through patching for easy installation. Ideal for premise wiring, telecommunications, data networking and Ethernet connections.

Description

Strengthen your high-speed network with Tripp Lite's N234-001-WH Cat6 Straight-Through Modular Compact In-Line Coupler. It connects two Cat6 patch cords to create one longer cable, and its compact in-line design is recommended for convenient feed-through patching. Built for ultra-fast performance, this is an ideal coupler when setting up premise wiring, voice/data networking, telecommunications and Ethernet connections.

Compatible with all Cat6 cables, the N234-001-WH features straight-through wiring and 50- μ inch gold-plated contacts designed to resist corrosion. The durable, high-impact polycarbonate housing resists scratching and is colored white to blend in with any color scheme. This coupler is UL-listed and meets all requirements for EIA/TIA Cat6 compliance. It's also backward compatible with Cat5e and Cat5 LANs.

Features

Strengthens Your High-Speed Network

- Ideal for premise wiring, voice/data networking, telecommunications and Ethernet connections
- Connects 2 Cat6 patch cables for a longer cable run
- Compact in-line design recommended for convenient feed-through patching
- Compatible with all Cat6 cables
- Backward compatible with Cat5e and Cat5 LANs

Superior Construction for Superior Performance

- Features straight-through wiring
- 50- μ inch gold-plated contacts resist corrosion and improve conduction

Highlights

- 50- μ inch gold-plated contacts on RJ45 jacks
- Heavy-duty polycarbonate housing
- Compact, clean-looking design
- Compatible with all Cat6 cables
- Backward compatible with Cat5e and Cat5 LANs

Package Includes

- N234-001-WH Cat6 Straight-Through Modular Compact In-Line Coupler (RJ45 F/F), White



- Durable, scratch-resistant polycarbonate housing
- White coloring blends into any color scheme
- UL-listed
- Meets all EIA/TIA Cat6 requirements

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332203410
Technology	Cat5/5e; Cat6
INPUT	
Cable Length (ft.)	0
Cable Length (m)	0
PHYSICAL	
Shipping Dimensions (hwd / in.)	0.500 x 4.000 x 5.300
Shipping Dimensions (hwd / cm)	1.27 x 10.16 x 13.46
Shipping Weight (lbs.)	0.2000
Shipping Weight (kg)	0.09
Color	White
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-40 to 154 F (-40 to 68 C)
Relative Humidity	10% to 90% RH, Non-condensing
CONNECTIONS	
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>