

DisplayPort to DVI-D Adapter Cable – M/M, DP with Latches, 1920 x 1200 (1080p) @ 60 Hz, 15 ft.

MODEL NUMBER: P581-015



DisplayPort to DVI-D cable converts a DisplayPort video signal for display on a DVI-D single-link monitor, projector or TV.

Features

DisplayPort to DVI-D Converter Sends HD Video to Your Current DVI-D Display Device

This 15-foot DisplayPort to DVI-D cable connects the DisplayPort output on your PC, laptop or Ultrabook to the DVI-D single-link input on your monitor, projector or television. No separate adapter or cable is needed. This allows you to continue using your existing DVI-D display for video without the expense of buying a new DisplayPort monitor.

Simple Solution for Displaying 1080p Video on a Large Screen or Secondary Monitor

The P581-015 is ideal for the office, classrooms, lecture halls and anywhere else you may need to connect your DisplayPort source to a DVI monitor. It also allows you to conveniently connect an additional monitor to your home or office workspace. The DisplayPort to DVI-D cable with durable molded ends supports high-definition video resolutions up to 1920 x 1200 (including 1080p) at 60 Hz.

Secures Tightly to Female Ports to Ensure a Secure Connection

Latches on the male DisplayPort plug and thumbscrews on the male DVI plug prevent the cable from being accidentally dislodged and interrupting vital video transmission.

Passive Adapter for Use with Dual-Mode DisplayPort Sources

This cable is a passive adapter that requires the connected computer to support DisplayPort++ (DP++). This allows DVI signals to be passed through. Check the documentation for your DisplayPort source for compatibility.

Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play DisplayPort to DVI-D converter requires no software, drivers or external power, works with both Windows and Mac operating systems, and is compatible with laptops and other devices equipped with a DisplayPort output that supports DP++. Its 15-foot length is helpful when an extended reach is needed, such as connecting to a projector.

3-Year Warranty

The P581-015 is backed by a 3-year warranty, ensuring reliability and performance.

Highlights

- Outputs DisplayPort video to your current DVI display to avoid expense of new monitor
- Delivers HD video quality at resolutions up to 1920 x 1200 (including 1080p) @ 60 Hz
- Extended 15 ft. length convenient for connecting to projectors and other far displays
- Plug-and-play operation with no software required for easy, immediate installation
- Passive adapter requires connected computer to have DP++ port for signal pass-through

Applications

- Use your existing DVI display with a new DisplayPort computer to avoid the expense of a new DisplayPort monitor
- Add a second monitor to your home or office workspace
- Video presentations in a classroom, lecture hall or conference room

System Requirements

- Source device with DisplayPort output that supports DisplayPort++
- Display device with DVI-D input
- Not for use with MST Hubs. For compatibility with MST Hubs, use a DisplayPort 1.2 compliant product, such as P581-006-V2.

Package Includes



- P581-015 DisplayPort to DVI-D Adapter Cable – M/M, DP w/Latches, 1920 x 1200 (1080p) @ 60 Hz, 15 ft.

Specifications

OVERVIEW	
UPC Code	037332213570
Technology	DVI; DisplayPort
INPUT	
Cable Length (ft.)	15
Cable Length (in.)	180
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.70
Shipping Weight (kg)	0.32
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32 to 158 F (0 to 70 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (MALE)
Connector Plating	Nickel
Contact Plating	Gold
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>