

## Heavy-Duty Fixed Security TV Wall Mount for 37-80" Televisions & Monitors - Flat/Curved, UL Certified

MODEL NUMBER: DWFSC3780MUL



Security wall mount with combination lock mounts your flat-panel or curved-screen television or monitor to the wall.

### Features

#### Security Wall Mount Hangs Your Flat-Panel or Curved-Screen TV or Monitor on the Wall

Ideal for home theaters, classrooms, conference rooms, hotels, bars, restaurants or anywhere else you may want to show off a television or monitor, this heavy-duty TV wall mount is hidden out of sight behind the display for a sleek, professional appearance. It fits most flat-panel or curved-screen displays from 37 to 80 inches and up to 88 pounds. Mounting hardware is included.

#### Durable All-Metal Construction Provides Convenient Cable Access

The fixed TV wall mount is constructed from heavy-duty steel with a powder-coated black finish that resists scratches. Rear openings with smooth edges enable easy access to cables. A built-in bubble level helps ensure your display is evenly mounted. This heavy-duty wall mount is function- and weight-tested to 200 pounds in accordance with UL Standard 2442.

#### Designed to Keep Your Display Safe and Secure

This security wall mount was conceived with your television or monitor's safety in mind, especially if the display is located in a public area with unguarded traffic, such as a library, classroom or hotel lobby. It comes with a solid steel security bar that slides through the mounting brackets and is secured into place with an included four-position combination lock.

#### Complies with VESA Standards

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing industry-wide standards for products like flat-panel TVs and monitors. To comply with these standards, most manufacturers use a series of universal mounting hole patterns, measured in millimeters, on the backs of the products. Measure the vertical and horizontal distances between the holes on the back of your display or refer to your display's owner's manual to find its VESA pattern. This monitor wall mount conforms to VESA-compliant displays with any of the following standard mounting hole patterns: 300 x 300, 400 x 200, 400 x 400 and 600 x 400.

#### 5-Year Warranty

The DWFSC3780MUL is backed by a 5-year warranty, ensuring reliability and performance.

### Highlights

- Accepts most popular flat- or curved-screen displays from 37 to 80 in. up to 88 lb.
- Function- and weight-tested in accordance with UL Standard 2442 up to 200 lb.
- Solid steel security bar and included combo lock deters tampering and theft
- Open architecture and built-in level enable easy cable access and accurate leveling
- Complies with VESA standards to ensure compatibility with your display

### Applications

- Mount a flat- or curved-screen television or monitor in an office lobby, conference room, bar, restaurant, airport or anywhere else digital signage is desired
- Secure an expensive display in a hotel lobby, classroom, library, hospital, truck stop or other public area with unguarded foot traffic

### Package Includes

- Wall plate
- (2) Adapter brackets
- Security bar
- Wall plate level
- (2) End caps
- (4) End cap screws
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws



- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (8) Large spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) 20 mm washers
- Combination lock
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332213730
PHYSICAL	
Mounting Location	Wall
Shipping Dimensions (hwd / in.)	29.30 x 9.10 x 2.00
Shipping Dimensions (hwd / cm)	74.42 x 23.11 x 5.08
Shipping Weight (lbs.)	7.10
Shipping Weight (kg)	3.22
Unit Dimensions (hwd / in.)	30.9 x 16.5 x .9
Unit Dimensions (hwd / cm)	78.5 x 42.0 x 2.2
Unit Weight (lbs.)	5.20
Unit Weight (kg)	2.36
Material of Construction	Steel
Color	Black
Screen Size Compatibility (in.)	37 - 80
Screen Size Compatibility (cm)	94.1 - 178.0
VESA Pattern (mm)	200x200; 300x300; 400x200; 400x400; 600x400
Motion	Fixed
Maximum Weight Capacity (lbs.)	200
Maximum Weight Capacity (kg)	91
FEATURES & SPECIFICATIONS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Tools Necessary	Yes
Cord Management	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>