

## Heavy-Duty Tilt Security Wall Mount for 32" to 55" TVs and Monitors, Flat or Curved Screens, UL Certified

MODEL NUMBER: DWTSC3255MUL



Security wall mount with combination lock mounts your flat-panel or curved-screen television or monitor to the wall.

### Features

#### Security Wall Mount Hangs Your Flat-Panel or Curved-Screen TV or Monitor on the Wall

Ideal for home theaters, classrooms, conference rooms, hotels, bars, restaurants or anywhere else you may want to show off a television or monitor, this heavy-duty TV wall mount is hidden out of sight behind the display for a sleek, professional appearance. It fits most flat-panel or curved-screen displays from 32 to 55 inches and 90lbs. Mounting hardware is included. Function and weight tested in accordance with UL Standard 2442 up to 150lbs.

#### Durable All-Metal Construction Provides Convenient Cable Access

The 55-inch-TV wall mount is constructed from heavy-duty steel with a powder-coated black finish that resists scratches. Rear openings with smooth edges enable easy access to cables. A built-in bubble level helps ensure your display is evenly mounted. This heavy-duty wall mount supports 99 pounds and is function and weight tested to 150 lbs. in accordance with UL Standard 2442.

#### Designed to Keep Your Display Safe and Secure

This heavy-duty wall mount was conceived with your television or monitor's security in mind, especially if the display is located in a public area with much unguarded traffic, such as a library, classroom or hotel lobby. It comes with a solid steel security bar that slides through the mounting brackets and is secured into place with an included three-position combination lock.

#### Tilt Feature Lets You Adjust the Viewing Angle to Your Specifications

You can adjust the horizontal angle of your display from  $-15^{\circ}$  to  $+10^{\circ}$ . This will minimize glare on the screen and allow you to customize the angle for comfortable viewing.

#### Complies with VESA Standards

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing industry-wide standards for products like flat-panel TVs and monitors. To comply with these standards, most manufacturers use a series of universal mounting hole patterns, measured in millimeters, on the backs of the products. Measure the vertical and horizontal distances between the holes on the back of your display or refer to your display's owner's manual to find its VESA pattern. This 55-inch-TV wall mount conforms to VESA-compliant displays with any of the following standard mounting hole patterns: 200 x 200, 300 x 300, 400 x 200 and 400 x 400.

### Highlights

- Accepts most popular flat- or curved-screen displays from 32 to 55 in. 99lbs.
- In addition, function and weight tested in accordance with UL standard 2442 up to 150lbs
- Solid steel security bar and included combo lock deters tampering and theft
- Heavy-duty steel construction designed for long life and to resist wear and tear
- Open architecture and built-in level enable easy cable access and accurate leveling
- Tilts  $-15^{\circ}$  to  $+10^{\circ}$  to minimize glare and provide comfortable custom viewing angles

### Applications

- Mounting a flat- or curved-screen television or monitor in an office lobby, conference room, bar, restaurant, airport or anywhere else digital signage is desired
- Securing an expensive display in a hotel lobby, classroom, library, hospital, truck stop or other public area with much foot traffic

### Package Includes

- Wall plate
- (2) Adapter brackets
- Security bar
- (2) End caps
- (4) End cap screws



#### 5-Year Warranty and Environmentally Responsible Design

The DWTSC3255MUL comes with a 5-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (4) Washers
- (8) Small spacers
- (8) Large spacers
- (4) Anchor bolts
- (4) Concrete anchors
- (4) 20 mm washers
- Combination lock
- Hex key
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332213723
PHYSICAL	
Mounting Location	Wall
Shipping Dimensions (hwd / in.)	21.60 x 6.50 x 2.20
Shipping Dimensions (hwd / cm)	54.86 x 16.51 x 5.59
Shipping Weight (lbs.)	6.60
Shipping Weight (kg)	2.99
Unit Dimensions (hwd / in.)	20.3x17.3 x 2.3
Unit Dimensions (hwd / cm)	51.5 x 44.0 x 5.9
Unit Weight (lbs.)	5.20
Unit Weight (kg)	2.36
Material of Construction	Steel
Color	Black
Screen Size Compatibility (in.)	32 - 55
Screen Size Compatibility (cm)	94.1 - 178.0
VESA Pattern (mm)	200x200; 300x300; 400x200; 400x400
Motion	Tilt



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Maximum Weight Capacity (lbs.)	150
Maximum Weight Capacity (kg)	68
<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
Cord Management	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>