

## USB-C to Gigabit Network Adapter with USB-C PD Charging - Thunderbolt 3, Black

MODEL NUMBER: U436-06N-GB-C



USB to LAN converter adds Gigabit Ethernet and USB-C charging ports to your laptop, MacBook or other compatible device.

### Features

**USB to Ethernet Converter Connects to Your Device's USB-C or Thunderbolt 3 Port**

**Accesses a Wired Gigabit Ethernet Network**

**Charges a Connected Device**

**Built-In USB-C Cable Connects in Either Direction**

**Ready to Use Right Out of the Package**

**3-Year Warranty and Environmentally Responsible Design**

### Highlights

- Connects you to a wired Ethernet network when no Wi-Fi is available
- Supports USB 3.1 Gen 1 for fast data uploads and downloads up to 5 Gbps
- Widely compatible with Windows, Mac and Chromium computers
- Powers and charges PD Charging-compliant devices, such as MacBooks and Chromebooks
- Easy installation with plug-and-play operation—no software required

### Applications

- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Upload data from your notebook or download data from the Ethernet at true 10/100/1000 Mbps Ethernet speeds
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port

### System Requirements

- Tablet, laptop, Chromebook, MacBook, smartphone or PC with USB-C or Thunderbolt 3 port
- Windows, Mac or Chromium operating system

### Package Includes

- U436-06N-GB-C USB-C to



Gigabit Network Adapter with  
USB-C PD  
Charging—Thunderbolt 3, Black  
• Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332209221
Technology	Cat5/5e; Cat6; USB 3.1 (Gen 1); USB
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (ft.)	0.5
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power), Orange (Activity)
PHYSICAL	
Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Shipping Weight (lbs.)	0.00
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	0.57 x 1.6 x 1.58
Unit Weight (lbs.)	0.1
Unit Weight (kg)	0.05
Material of Construction	ABS, PVVC
Color	Black
Cable Jacket Rating	VW-1
ENVIRONMENTAL	
Operating Temperature Range	32 to 158 F (0 to 70 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	3.1 BTU/Hr
Power Consumption (Watts)	0.9



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C)
<b>COMMUNICATIONS</b>	
Network Speed	1Gbps
IEEE Standards Supported	802.3; 802.3az; 802.3u; 802.3x
<b>CONNECTIONS</b>	
Ports	2
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	Cat5/5e/6 Cables
UASP Support	No
USB Power Delivery (PD) Charging Support	Yes
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>