

For Patient-Care Vicinity – UL 1363A Medical-Grade Power Strip, 4 15A Hospital-Grade Outlets, Safety Covers, 7 ft. Cord

MODEL NUMBER: PS-407-HG-OEM



Supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care vicinities.

Description

The PS-407-HG-OEM Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets that include locking safety covers.

Anti-Microbial Protected with EPA Registered and FDA Compliant Silver Ionic Technology known to inhibit growth of Microbes on surfaces.

Two built-in resettable 15A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The seven-foot power cord provides ample reach to the AC power source.

Mounting tabs and flanges let you install the PS-407-HG-OEM on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

Features

Power Distribution Anywhere in Any Medical Facility

- Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas
- For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted
- 120V, 50/60 Hz power strip complies with UL 1363A specifications

Versatile Medical-Grade Solution

- 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power

Highlights

- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A specifications
- 4 NEMA 5-15R-HG outlets with locking safety covers
- 7 ft. cord with NEMA 5-15P-HG plug reaches nearby outlets
- Easy to mount on a variety of surfaces, e.g. IV poles
- Exclusive, patented anti-microbial coating - 99.9% effective in inhibiting bacteria and viruses

Package Includes

- PS-407-HG-OEM UL 1363A Medical-Grade Power Strip, 7 ft. cord
- Owner's manual



- 7 ft. power cord with NEMA 5-15P-HG hospital-grade plug provides ample reach to the power source
- Rugged, all-metal housing for long life in demanding environments

Premium Safety Features

- Included locking outlet safety covers block access to unused outlets
- Dual resettable built-in 15A circuit breakers protect against dangerous overloads
- Switchless design prevents accidental shutoff

Ready to Use Right Out of the Box

- Built-in mounting tabs and flanges for easy installation on a variety of surfaces

Exclusive, Patented Antimicrobial Protection

- Silver ionic powder coating is 99.9% effective in inhibiting the growth of bacteria like C. diff and MRSA
- Patented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in hospitals and other medical environments
- Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Specifications

| OVERVIEW | |
|------------------------------------|--|
| UPC Code | 037332203632 |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (4) 5-15R-HG |
| Circuit Breaker (amps) | 15 |
| Overload Protection | 2 x 15amp breakers (1 line, 1 neutral) |
| Outlet Orientation | Single row of 4 |
| Right-Angle Outlets | No |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 15A, 120V |
| Input Connection Type | NEMA 5-15P-HG |
| Input Cord Length (ft.) | 7 |
| Input Cord Length (m) | 2.13 |
| Input Cord Gauge Type | 14 gauge, SJT |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|---------------------------|
| Voltage Compatibility (VAC) | 120 |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | No power switch |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 2.20 x 6.10 x 9.80 |
| Shipping Dimensions (hwd / cm) | 5.59 x 15.49 x 24.89 |
| Shipping Weight (lbs.) | 2.30 |
| Shipping Weight (kg) | 1.04 |
| Unit Dimensions (hwd / in.) | 8.65 x 2.5 x 1.5 |
| Unit Dimensions (hwd / cm) | 21.97 x 6.35 x 3.81 |
| Unit Weight (lbs.) | 2.77 |
| Unit Weight (kg) | 1.26 |
| Material of Construction | Metal |
| Receptacle Color | White |
| Color (AC Line Cord) | White |
| Outlets Measurement (Center to Center) | Inner outlets = 32.5mm |
| Anti-Microbial Protected | Yes |
| CERTIFICATIONS | |
| Approvals | TUV tested to UL 1363A |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>