

# Coupler connector - UC-12P2N1290DU - 1606326

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Coupling connector, straight, shielded: yes, Screw locking, M23, No. of pos.: 12, type of contact: Pin, Solder connection, cable diameter range: 2 mm ... 14.5 mm

The figure shows the 12-pos. product version with standard contact chamber numbering



## Key Commercial Data

|              |   |
|--------------|---|
| Packing unit | 20 pc   |
| GTIN         | <br>4 046356 258869 |
| GTIN         | 4046356258869   |


## Technical data

### Environmental Product Compliance


|            |   |
|------------|---|
| REACH SVHC | Lead 7439-92-1  |
| China RoHS | Environmentally Friendly Use Period = 50  |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

## Drawings

Schematic diagram



Dimensional drawing



## Coupler connector - UC-12P2N1290DU - 1606326

### Approvals

Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

|     |   |         |
|-----|---|---------|
| EAC |  | B.01742 |
|-----|---|---------|

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>