

Electronic housing - UM-BASIC PROFILE - 2200149

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Press-drawn section housings, length: 2000 mm, Lower part, color: light gray, height: 40 mm, Note: required profile length = PCB length - 16.2 mm



Your advantages

- ✓ Item is from the UM-BASIC/UM-PRO product range
- ✓ PVC press-drawn section (UM-BASIC) or PA (UM-PRO)
- ✓ Available in individual lengths
- ✓ Available in the overall widths of 72 mm, 108 mm, and 122 mm
- ✓ Variety of connection technologies
- ✓ Can be mounted on the DIN rail

Key Commercial Data

Packing unit	1 pc
--------------	------

Configuration

Profile PCB width	122 mm [UM122]
Profile length [cm]	7.62
profile color	Light gray [GY7035]

Technical data

General

Housing type	Press-drawn section housings
Housing material	PVC
Color (RAL)	light gray

Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C (depending on power dissipation)
---------------------------------	---

Dimensions

Length	2000 mm
Height	40 mm

Electronic housing - UM-BASIC PROFILE - 2200149

Technical data

Dimensions

Depth	127.5 mm
-------	----------

Technical data

Number of positions	999
---------------------	-----

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>