

Plug-in bridge - FBS 1/4/7/10-6 - 3030383

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Plug-in bridge, pitch: 6.2 mm, width: 60.3 mm, number of positions: 10, pin assignment: 1, 4, 7, 10, color: red

Your advantages

The 2- to 50-pos. jumpers can bridge up to 50 terminal blocks in the two bridge shafts of the CLIPLINE complete system in one step

RoHS

Key Commercial Data

Packing unit	10 pc
GTIN	4 046356 990363
GTIN	4046356990363

Technical data

Technical data

Color	red
Material	Copper
Number of positions	10
Pin assignment	1, 4, 7, 10
Pitch	6.2 mm
Height	23 mm
Width	60.3 mm
Flammability rating according to UL 94	V0
Maximum load current	32 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
Standards and Regulations	
Flammability rating according to UL 94	V0
Environmental Product Compliance	
China RoHS	Environmentally friendly use period: unlimited = EFUP-e



Plug-in bridge - FBS 1/4/7/10-6 - 3030383

Technical data

Environmental Product Compliance

No hazardous substances above threshold values

Phoenix Contact 2018 © - all rights reserved http://www.phoenixcontact.com

PHOENIX CONTACT GmbH & Co. KG Flachsmarktstr. 8 32825 Blomberg Germany Tel. +49 5235 300 Fax +49 5235 3 41200 http://www.phoenixcontact.com