

Series 7400 Kraftform Torque Screwdrivers



EAN:	4013288161383	Size:	260x220x85 mm
Part number:	05350451001	Weight:	1022 g
Article number:	7445/46/47	Country of origin:	CZ
		Customs tariff number:	82079030

- Kraftform torque screwdriver set
- Suitable for bits with 1/4" hex head drive
- With Hex-Plus, TORX® and TORX PLUS® bits

Wera torque screwdriver set. Two high precision torque screwdrivers with variable torque settings. One torque screwdriver with Kraftform pistol handle for the transfer of especially high torque; multi-component for high working speeds and particularly ergonomic screwdriving. Simple adjustment of the required torque value without any special tools. Easy-to-read scale value. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Kraftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Includes a bit assortment in a high quality and stable plastic case.

Web link


http://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7445_46_47.html

Wera - 7445/46/47
05350451001 - 4013288161383

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de


Series 7400 Kraftform Torque Screwdrivers


Set contents:


 **7400 inch**
 05074710001 1 x 7445x2.5-11.5
 05074711001 1 x 7446x11.0-29.0


 **7400 Pistole inch**
 05074712001 1 x 7447x25.0-55.0





 **867/1 TZ TORX®**
 05066301001 1 x TX 6x25
 05066302001 1 x TX 7x25
 05066303001 1 x TX 8x25
 05066304001 1 x TX 9x25
 05066305001 1 x TX 10x25
 05066308001 1 x TX 15x25
 05066310001 1 x TX 20x25
 05066312001 1 x TX 25x25
 05066315001 1 x TX 30x25



 **867/1 IP TORX PLUS®**
 05066274001 1 x 6 IPx25
 05066276001 1 x 7 IPx25
 05066278001 1 x 8 IPx25
 05066279001 1 x 9 IPx25
 05066280001 1 x 10 IPx25
 05066282001 1 x 15 IPx25
 05066284001 1 x 20 IPx25
 05066286001 1 x 25 IPx25
 05066288001 1 x 30 IPx25



 **840/1 Z Hex-Plus**
 05056305001 1 x 2.0x25
 05056310001 1 x 2.5x25
 05056315001 1 x 3.0x25
 05056320001 1 x 4.0x25
 05056325001 1 x 5.0x25
 05056330001 1 x 6.0x25



Web link

http://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7445_46_47.html

Wera - 7445/46/47
 05350451001 - 4013288161383

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Series 7400 Kraftform Torque Screwdrivers

Torque Tools

Adjustable Torque Screwdrivers



Wera's torque tools offer torque-controlled screw tightening so as to avoid damage to the screw or workpiece and to ensure the integrity of the screw connection. This makes work-intensive drilling-out of screws and unproductive downtimes a thing of the past. It is also important whenever repeat accuracy is required. They come with an ergonomic Kraftform handle and have a distinctly audible and perceptible click signal whenever the required torque value is reached. No time-consuming blade changes; instead of special blades, conventional bits conforming to C 6,3 and E 6,3 or even ¼" sockets can be used.



They can be adjusted by hand to the corresponding scale value. Also available in ESD version (also with take-up for HIOS/Halfmoon bits) and with Kraftform Micro handle.



Wera's adjustable torque screwdrivers allow variable torque settings with maximum precision and ensure that the user gets the very best results in the familiar Wera design with superior ergonomics.

Web link

http://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7445_46_47.html

Wera - 7445/46/47
05350451001 - 4013288161383

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Series 7400 Kraftform Torque Screwdrivers

Adjustable Torque Screwdrivers

Simple setting

Easy-to-read

Measurement accuracy



Many screws – particularly in assembly and maintenance applications – have to be tightened with controlled torque to ensure the dependability of the screw connection and/or to avoid damage to the screw or work piece. Wera's adjustable torque screwdrivers are the ideal tool for this. They feature a torque range of 0.3 Nm to 8.8 Nm, two different handles, measurement accuracy of $\pm 6\%$ and Rapidaptor technology for rapid bit change.

Simple setting of the required torque by hand.

Easy-to-read scale value.

Measurement accuracy is $\pm 6\%$ in accordance with the standard DIN EN ISO 6789. Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Web link

http://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7445_46_47.html

Wera - 7445/46/47
05350451001 - 4013288161383

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de