

02

0271


Quicklock circular connectors, IP67



Quicklock chassis socket, IP67, size 16, straight version,  
with plastic housing, solder terminals and protecting cap  
(IP65)

02

0271



\*a port

**Environmental conditions**

Temperature range -40 °C/+80 °C

**Materials**

Insulating body	PBT, V-0 according to UL94
Contact bush	CuSn, gold-plated
Housing	PBT, V-0 according to UL94
Cap	SI
Hexagonal nut	PBT, V-0 according to UL94

**Mechanical data**

Mating cycles	1700
Insertion force	≤ 90 N
Withdrawal force	≤ 40 N
Protection class	IP67 (protecting cap IP65)

**Electrical data (at T<sub>amb</sub> 20 °C)**

Contact resistance	≤ 5 mΩ
Rated current	10 A (2-4 poles) 5 A (5-9 poles)
Rated voltage	400 V
Rated impulse voltage	2500 V AC
Creepage distance	≥ 2 mm
Clearance	≥ 2 mm
Insulation resistance	> 500 MΩ

**Associated products**

Counterparts  
☞ 0251

02

0271

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
0271 02	2	10	50
0271 03	3	10	50
0271 04	4	10	50
0271 05	5	10	50
0271 07	7	10	50
0271 08	8	10	50
0271 09	9	10	50

**Packaging:**

in individual plastic bags, in a cardboard box