



BURNDY Catalog Number
UPC Number

Description
Status

Web Use
BURNDY Product Line

Width (in)
Length (in)
Height (in)

Weight lbs

Warranty

Product Description

ROHS Compatible
CULUS

Pressure (Operating)
Crimp Force
Force Developed
Operating Voltage

Documentation

Literature

PATMD68LI
7818105288777
WIRE LUG CRIMPING TOOL W/
D3/O GROOVES
Active

Dimensional

2.8
21.3
4.25

General

7.5
5-year limited warranty; 1 year on
battery and charger; Lifetime on
INFINITY DRIVE®;
Wire lug crimping tool, 6 Tons,
Ergonomically Balanced Tool

Approvals / Certifications

Exempt
N

Physical

7800
6 tons (5.4 metric tons)
6 tons
18 VDC

- [LITHIUM-ION BATTERY MSDS](#)

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175