



BURNDY Catalog Number GAR1929
UPC Number 7818102360000
Description 2/0-250CU 2 1/2IPS
Status Active

Web Use
 BURNDY Product Line

Dimensional	
Width (in)	4.19
Length (in)	1.81
Height (in)	5.00
Size (Hex) or Size (Bolt)	3/8
Size (Hex) or Size (Bolt) - in	0.38
B Length (in)	3.25
Width (Fraction)	4-1/4
Height (Fraction) (in)	5
General	
Product Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 2-1/2" to 2-7/8" Rod, 2-1/2" Pipe, Bright Dipped
Other	
Type of U Bolt	266
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL467
Rated for Direct Burial	Y
Conductor(s)	
Copper Tube Size (SCH40) - Range	2 1/2 IPS IPS
Rod Size (Range)	2 1/2 in-2 7/8 in
Copper Solid Size (Range)	2/0 AWG-4/0 AWG
Copper Stranded (Range)	1/0 -250 kcmil
Rebar Size (Range)	N/A
Physical	
Type of Hardware	DURIUM® Silicon Bronze
Installation Torque	240
Type of Plating	Bright Dipped
Plated (Yes or No)	N
Product Material	Copper Alloy
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175