



BURNDY Catalog Number
UPC Number
Description
Status

KS173
 7818100215077
 SERVIT 8 STR - 6 SOL
 Active

Web Use
 BURNDY Product Line

Dimensional	
Width (in)	0.70
Cross Flats	.62
General	
Product Description	Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap)
Conductor(s)	
Copper Tap Range	16 AWG-6 AWG
CopperWeld Solid Run Size (Range)	N/A
Copper Stranded Run (Range)	8 AWG-6 AWG
CopperWeld Stranded Tap Size (Range)	8 D AWG-6 A AWG
Copper Solid Tap (Range)	N/A
CopperWeld Solid Tap Size (Range)	N/A
Copper Solid Run Size (Range)	6 AWG
CopperWeld Stranded Run Size (Range)	N/A
Physical	
Installation Torque	165
Type of Plating	Unplated
Connector Type	Split Bolt
Plated (Yes or No)	N
Approvals / Certifications	
UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	RUS
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175