



BURNDY Catalog Number
UPC Number
Description
Status

KC25B1
 7818102558033
 2-1/0 STR 1 1/16 POST 1
 Active

Web Use
 BURNDY Product Line

Dimensional

Stud Length (in) 1-1/16,1.04
 Thread Size 1/2-13
 Height (in) 1.19
 D or Diameter (Fraction) (in) 1-1/4
 Nut Width (Fraction) 15/16
 Nut Width (in) 0.93
 D - in 1.25
 Body Width (Fraction) 3/4
 Body Width (in) 0.75
 Height (Fraction) (in) 1-1/8

General

Mechanical Grounding Connector,
 Cable to Flat, 2-1/0 AWG (Str) / 2-
 2/0 AWG (Sol), Stud dia:1/2-13

Conductor(s)

2 AWG-2/0 AWG
 2 AWG-1/0

Physical

Unplated
 N
 Leaded Bronze Alloy

Approvals / Certifications

Rated for Direct Burial Y
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Exempt
 UL Recognized N
 CULUS N
 Industry Standards UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175