



BURNDY Catalog Number
UPC Number
Description
Status

PAT81KFTLI
7818105053800
4-POINT(R) LITHIUM-ION
Active

Web Use
BURNDY Product Line

Dimensional	
Width (in)	3.2
Length (in)	15.6
Height (in)	14.1
General	
Weight lbs	13.2
Warranty	5 years on tool; 1 year on battery and charger; Lifetime on INFINITY DRIVE®
Product Description	Dieless Crimper, 6 Ton, 18 V-DC, Recharge Time 45 mins.
Approvals / Certifications	
ROHS Compatible	Exempt
CULUS	N
Physical	
Pressure (Operating)	7800
Crimp Force	6 tons (5.4 metric tons)
Force Developed	6 tons
Operating Voltage	18 VDC
Documentation	
Literature	<ul style="list-style-type: none"> LITHIUM-ION BATTERY MSDS

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175