



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

PATMD68LIDC  
7818105292944  
INLINE TOOL D3\_0, 12V CH  
Active

**Web Use**  
BURNDY Product Line

Width (in)  
Length (in)  
Height (in)

**Dimensional**

6.9  
20.91  
5.48

Weight lbs

**General**

7.8  
5-year limited warranty; 1 year on battery and charger; Lifetime on INFINITY DRIVE®; Wire lug crimping tool, 6 Tons, Ergonomically Balanced Tool, Battery Voltage: 18 VDC

Warranty

Product Description

**Approvals / Certifications**

Exempt  
N

ROHS Compatible  
CULUS

**Physical**

Pressure (Operating)  
Crimp Force  
Force Developed  
Operating Voltage

7800  
6 tons (5.4 metric tons)  
6 tons  
14.4 VDC

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175