



BURNDY Catalog Number
UPC Number
Description
Status

C4
 7818101423255
 2-1/2 TO 4IN GRDCMP BARE
 Active

Web Use
 BURNDY Product Line

Pipe Size (Range)
 Width (in)
 Length (in)
 Height (in)
 Pad Width (in)

Dimensional

2 1/2 in-4 in
 0.96
 6.25
 4.13
 1.88

Product Description

General

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 2-1/2" - 4" Water Pipe

Copper Solid Size (Range)
 Copper Stranded (Range)
 Rebar Size (Range)

Conductor(s)

10 AWG-2 AWG
 10 AWG-2 AWG
 N/A

Type of Hardware
 Type of Plating
 Ground Strap
 Plated (Yes or No)
 For Armored Cable
 Product Material

Physical

DURIUM® Silicon Bronze
 Unplated
 N
 N
 N
 Bronze Alloy

Recommended Installation Torque - Wire Clamp

50

Recommended Installation Torque - Pipe

50

Approvals / Certifications

UL Listed
 CSA Certified
 Rated for Direct Burial
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Y
 Y
 N
 Exempt
 N
 N
 UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday

Phone: 800-346-4175