



TYPE	A	B
L02	59	46
L04	94.5	79
L06	129.5	114
L08	163	148
L10	200	183

Product #: 3730660

Order Symbol: L 02

Description: Window for 2 modules

Remarks: Clear cover

Dimensions	Length	Width	Height
Inch	0.04	3.03	2.36
mm	1	77	60

Materials

Material:	Polycarbonate
Base color:	RAL 7035 -light grey
Cover color:	Clear

Temperatures

Temperature °F (continuous):	°F : -40 ... 175
------------------------------	------------------

Ratings

Ingress Protection (EN 60529):	IP 65
Impact Resistance (EN 62262):	IK08
Halogen free (DIN/VDE 0472, Part 815):	No