

2ft (60cm) Heavy Duty Extension Cord, IEC 60320 C19 to C20 Black Extension Cord, 20A 250V, 12AWG, Heavy Gauge Power Extension Cable, AC Power Cable - UL Listed Components

Product ID: BA16-2200-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Heavy Duty power cord supports high-powered equipment and PDUs
- Extend a server or rackmount equipment power cord by an additional 2ft

Features

- **HEAVY DUTY POWER CORD:** 2ft (60cm) 12AWG heavy gauge power cord with IEC 60320 C19 to C20 connector is suitable for servers or other high-powered equipment; Indoor use; Rated to carry 250V at 20A
- **BUILT FOR PERFORMANCE AND SAFETY:** Made with UL Listed components; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 2ft (60cm); TAA Compliant; IEC 60320 C19 to IEC 60320 C20; 12AWG; 250V 20A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.44in (11.2mm)
- **COMPATIBILITY:** IEC 60320 C19 to C20 Power extension cord works with North American PDUs and high-powered devices; Extend a power connection to a UPS, Power Supply/PDU, or high-power device; Replacement heavy duty power cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C19 to C20 power cord is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C20 Power
Connector B	1 - IEC 60320 C19 Power

Power

Input Voltage	250V AC
Input Current	20A

Environmental

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

Physical Characteristics

Color	Black
Wire Gauge	12 AWG
Cable Length	2.0 ft [0.6 m]
Cable OD	0.4 in [11.2 mm]
Product Length	24.0 in [61.0 cm]
Product Width	1.3 in [3.4 cm]
Product Height	1.0 in [2.6 cm]
Weight of Product	0.0 oz [0.0 g]

Packaging Information

Package Length	5.7 in [14.5 cm]
Package Width	11.5 in [29.3 cm]
Package Height	1.3 in [3.3 cm]
Shipping (Package) Weight	7.1 oz [200.0 g]

What's in the Box

Included in Package	1 - 2ft C19 to C20 Heavy-Duty Power Cord
---------------------	--

**Product appearance and specifications are subject to change without notice.*