

10ft (3m) Power Extension Cord, NEMA 5-15P to NEMA 5-15R AC Power Cable, 10A 125V, 18AWG, Outlet Extension Power Cable, Black Extension Cord, AC Power Cord - UL Listed Components

**Product ID:** 231A-8A00-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

## Certifications, Reports and Compatibility



## Applications

- Extend a monitor, scanner, printer, or PC power cord by an additional 10 ft
- Extend a power connection from a crowded PDU for more convenient access

## Features

- **POWER EXTENSION CORD:** 10ft (3m) 18AWG Universal Power Extension Cord with NEMA 5-15P to NEMA 5-15R connector is suitable for workstations/home office; Indoor use; Rated to carry 125V at 10A
- **BUILT FOR PERFORMANCE AND SAFETY:** Made with UL Listed components; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 10ft (3m); TAA Compliant; NEMA 5-15P to NEMA 5-15R; 18AWG; 125V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.31in (7.8mm)
- **COMPATIBILITY:** Extend the length of a power cord from your desktop computer, server, or printer to a wall outlet or PDU; NEMA 5-15P plug works with North American electrical outlets; Replacement AC power extension cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This 5-15P to 5-15R power cord is available in other lengths

---

### Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

---

### Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - NEMA 5-15 Power (North America)

---

### Power

Input Voltage	125V AC
---------------	---------

Input Current	10A
---------------	-----

---

**Environmental**

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

---

**Physical Characteristics**

Color	Black
Wire Gauge	18 AWG
Cable Length	10.0 ft [3.0 m]
Cable OD	0.3 in [7.8 mm]
Product Length	10.0 ft [3.0 m]
Product Width	1.1 in [2.7 cm]
Product Height	1.4 in [3.5 cm]
Weight of Product	0.0 oz [0.0 g]

---

**Packaging Information**

Package Length	5.7 in [14.5 cm]
Package Width	11.4 in [29.0 cm]
Package Height	3.1 in [8.0 cm]
Shipping (Package) Weight	11.3 oz [320.0 g]

---

**What's in the Box**

Included in Package	1 - 10ft NEMA 5-15P to NEMA 5-15R Power Cord
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***