

6ft (1.8m) Hospital-Grade Extension Cord, Green Dot Medical Power Cable, NEMA 5-15P to NEMA 5-15R, 13A 125V, 16AWG, Gray Power Extension Cable - UL Listed Components

Product ID: 231B-660H-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Ideal for use in hospitals and medical environments
- Extend a power connection in a hospital or medical setting
- Green dot marking is UL Listed for guaranteed safety and durability
- Green Dot medical power cable for optimal safety and durability

Features

- **HOSPITAL-GRADE POWER CORD:** 6ft (1.8m) 16AWG Green Dot Power Extension Cord with NEMA 5-15P to NEMA 5-15R connector is safe for hospitals and medical environments; Easy Grip molding for safe handling and frequent use; Indoor use; Rated to carry 125V at 13A
- **BUILT FOR PERFORMANCE AND SAFETY:** Made with UL Listed components with Green Dot indicator for use in hospitals and medical settings; VW-1 Fire Rated cable w/molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.8m); TAA Compliant; NEMA 5-15P to NEMA 5-15R; 16AWG; 125V 13A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.33in (8.5mm)
- **COMPATIBILITY:** NEMA 5-15P plug works with North American electrical outlets; Extend a 3-prong power cable connection, or safely connect hospital or medical equipment to a wall outlet or PDU
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this hospital-grade extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
-------------	-------------------------------------

Connector B 1 - NEMA 5-15 Power (North America)

Power

Input Voltage	125V AC
Input Current	13A
Output Current	13A

Environmental

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

Physical Characteristics

Color	Gray
Wire Gauge	16 AWG
Cable Length	6.0 ft [1.8 m]
Cable OD	0.3 in [8.5 mm]
Product Length	6.0 ft [1.8 m]
Product Width	1.1 in [2.7 cm]
Product Height	1.3 in [3.4 cm]
Weight of Product	0.0 oz [0.0 g]

Packaging Information

Package Length	5.7 in [14.5 cm]
Package Width	11.4 in [29.0 cm]
Package Height	2.8 in [7.0 cm]
Shipping (Package) Weight	8.5 oz [240.0 g]

What's in the Box

Included in Package	1 - 6ft Hospital-Grade Power Extension Cord
---------------------	---

**Product appearance and specifications are subject to change without notice.*

