



BURNDY Catalog Number
UPC Number

PATMD6814V
7818104498200
BATTERY ACTUATED CRIMPER
W/D3/O GROOVE
Active

Description
Status

Web Use
BURNDY Product Line

Dimensional	
Width (in)	3.69
Length (in)	20.91
Height (in)	5.48
General	
Weight lbs	7.8
Warranty	5-year limited warranty; 1 year on battery and charger; Lifetime on INFINITY DRIVE#0174;
Product Description	Battery Actuated Crimping Tool, Hydraulic Self Contained, 6 Ton Output Force, 10 AWG(Sol) - 2/0 AWG Copper, 8 AWG-350 kcmil Aluminium, 14 AWG(Sol)-4/0 ACSR, 14.4V Ni-MH
Approvals / Certifications	
ROHS Compatible	Exempt
CULUS	N
Physical	
Pressure (Operating)	7800
Crimp Force	6 tons (5.4 metric tons)
Force Developed	6 tons
Operating Voltage	14.4 VDC
Documentation	
Literature	<ul style="list-style-type: none"> NI-MH18Vand14VMAKITABATTERYMSDS

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175