



BURNDY Catalog Number
UPC Number
Description
Status

PAT750XT18V
 7818104387011
 CRIMPER, 12T, 18V NiMH
 Active

Web Use
 BURNDY Product Line

Dimensional	
Width (in)	3.5
Length (in)	15.75
Height (in)	13.5

General	
Weight lbs	16.5
Warranty	5 years on tool; 1 year on battery and charger; Lifetime on INFINITY DRIVE® #0174; Battery Actuated Crimping Tool, Hydraulic Self Contained, 12 Ton Output Force, 14 AWG-750 kcmil Copper, 8 AWG - 750 kcmil Aluminium, 4 AWG - 556.5 kcmil ACSR, 18V Ni-MH, 1/2" - 1" Ground Rod
Product Description	

Approvals / Certifications	
ROHS Compatible	Exempt
CULUS	N

Physical	
Pressure (Operating)	10000
Crimp Force	12 tons
Force Developed	12 tons
Operating Voltage	18 VDC

Documentation

Literature

- [NI-MH18Vand14VMAKITABATTERYMSDS](#)

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175