



BURNDY Catalog Number
UPC Number
Description
Status

KLU300
 7818103514200
 1/0-350 CU LUG
 Active

Web Use
 BURNDY Product Line

Dimensional	
Screw Size	5/8
Length (in)	2.83
Size (Hex) or Size (Bolt)	5/8
Stud Size (in)	3/8
Thickness	0.12
Size (Hex) or Size (Bolt) - in	0.63
B Length (in)	1.00
Pad Width (in)	0.99
N (in)	0.52
Hole Size (in)	0.39
Strip Length	1-5/8
B Length (Fraction)	1
General	
Product Description	Copper Terminal, Offset Tongue, 1 Hole, 1/0 AWG (Str)-350 kcmil, 3/8" Stud, 1 Screw
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	1/0 -350 kcmil
Physical	
Screw Type	Allen
Installation Torque	325
Type of Plating	Unplated
Connector Type	Terminal
Plated (Yes or No)	N
Product Material	Copper
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	Y
Industry Standards	UL467
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175