



BURNDY Catalog Number
UPC Number
Description
Status

C22
 7818101423188
 GRD CL BARE 1-1/4-2IN
 Active

Web Use
 BURNDY Product Line

Pipe Size (Range)
 Width (in)
 Length (in)
 Height (in)
 Pad Width (in)

Dimensional

1 1/4 in-2 in
 0.75
 3.63
 2.38
 1.00

Product Description

General

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1-1/4" - 2" Water Pipe

Copper Solid Size (Range)
 Copper Stranded (Range)
 Rebar Size (Range)

Conductor(s)

10 AWG-2 AWG
 10 AWG-2 AWG
 N/A

Type of Hardware
 Type of Plating
 Ground Strap
 Plated (Yes or No)
 For Armored Cable
 Product Material

Physical

DURIUM® Silicon Bronze
 Unplated
 N
 N
 N
 Bronze Alloy

Recommended Installation Torque - Wire Clamp

50

Recommended Installation Torque - Pipe

50

Approvals / Certifications

UL Listed
 CSA Certified
 Rated for Direct Burial
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Y
 Y
 N
 Compliant
 N
 N
 UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday

Phone: 800-346-4175