



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

GL2929  
 7818102600299  
 2/0SOL-250 2 COND TO BAR  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Width (in) 2.25  
 Height (in) 2.25  
 Size (Hex) or Size (Bolt) 1/2  
 Thickness 0.25  
 Size (Hex) or Size (Bolt) - in 0.50  
 B Length (in) 2.22  
 Width (Fraction) 2-1/4  
 Height (Fraction) (in) 2-1/4

**General**

Mechanical Grounding Connector,  
 2 Cables to 1/4" Thick Bar, 2/0  
 AWG (Sol) -250 kcmil, 1/2" Stud

**Conductor(s)**

1/4 in  
 2/0 AWG-4/0 AWG  
 2/0 AWG-250 kcmil

**Physical**

Installation Torque 480  
 Type of Plating Unplated  
 Plated (Yes or No) N  
 Product Material Copper

**Approvals / Certifications**

Rated for Direct Burial Y  
 UL Listed Y  
 CSA Certified N  
 ROHS Compatible Exempt  
 UL Recognized N  
 CULUS N  
 Industry Standards UL467

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175