



BURNDY Catalog Number
UPC Number
Description
Status

YA39L6
 7818101472766
 HYLUG-750KCMIL-1/2 STUD-
 Active

Web Use
 BURNDY Product Line

Dimensional

| | |
|---------------------|------------------|
| Tongue Angle | Straight |
| Length (in) | 3.41 |
| Barrell Style | Chamfered,Skived |
| Bolt Hole Size (in) | 0.52 |
| Barrel Type | Standard |
| Thickness | 0.27 |
| B Length (in) | 1.42 |
| Pad Width (in) | 1.91 |
| Strip Length | 1-15/16 |

General

| | |
|---------------------|---|
| Number of Holes | 1 |
| Product Description | Copper Compression Lug, 1 Hole w/ Inspection Window, 750 kcmil, 1/2" Stud, Short Barrel, Tin Plated |

Conductor(s)

| | |
|-----------------------------|-----------|
| Flex (Class G) Size - Range | N/A |
| Flex (Class H) Size - Range | N/A |
| Flex (Class I) Size - Range | N/A |
| Copper Solid Size (Range) | N/A |
| DLO Size (Range) | N/A |
| Copper Stranded (Range) | 750 kcmil |

Physical

| | |
|--------------------|----------------------|
| Type of Plating | Tin - Electro Plated |
| Color Code | Black |
| Plated (Yes or No) | Y |
| Index Number | 24 |
| Product Material | Copper |

Approvals / Certifications

| | |
|--------------------|-----------|
| UL Listed | Y |
| CSA Certified | Y |
| ROHS Compatible | Compliant |
| UL Recognized | N |
| CULUS | N |
| Industry Standards | UL467 |

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175