



**BURNDY Catalog Number**  
**UPC Number**

PATMD614V  
7818104498133  
BATTERY ACTUATED CRIMPER  
W/D3/BG GROOVE  
Active

**Description**  
**Status**

**Web Use**  
BURNDY Product Line

#### Dimensional

Width (in) 3.69  
Length (in) 20.91  
Height (in) 5.48

#### General

Weight lbs 7.8  
Warranty 5-year limited warranty; 1 year on battery and charger;  
Lifetime on INFINITY DRIVE&#0174;  
Product Description Battery Actuated Crimping Tool, Hydraulic Self Contained, 6  
Ton Output Force, 10 AWG(Sol)-500 kcmil Copper, 8 AWG-  
350 kcmil Aluminium, 14 AWG-4/0 ACSR, W Dies, 14V Ni-MH

#### Approvals / Certifications

ROHS Exempt  
Compatible  
CULUS N

#### Physical

Pressure (Operating) 7800  
Crimp Force 6 tons (5.4 metric tons)  
Force  
Developed 6 tons  
Operating Voltage 14.4 VDC

#### Documentation

Literature • [/burndy/documentation/2011\\_burndy\\_tooling\\_catalog](/burndy/documentation/2011_burndy_tooling_catalog)

For further technical assistance, please contact us

#### BURNDY LLC - USA

47 East Industrial Park Drive  
Manchester NH 03109

#### BURNDY Technical Services

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175