



<b>BURNDY Catalog Number</b>	GSTUD34HY
<b>UPC Number</b>	7818102209000
<b>Description</b>	250-500, WITH YGHP-C34
<b>Status</b>	Active

**Web Use**  
BURNDY Product Line

	<b>Dimensional</b>
Tongue Angle	45 Degree
Length (in)	5.81
Thickness	0.51
B Length (in)	0.76
Diameter (in) - Total	0.75

	<b>General</b>
Product Description	Structural Steel Grounding Connector, 4/0 AWG, 3/4" Rod

	<b>Conductor(s)</b>
Electrical Equivalent Conductor Size	4/0
Copper Stranded (Range)	4/0 AWG

	<b>Physical</b>
Type of Plating	Nickel
Plated (Yes or No)	Y
Product Material	Steel

	<b>Approvals / Certifications</b>
Rated for Direct Burial	N
UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175