



BURNDY Catalog Number
UPC Number
Description
Status

YGF292N
 7818102205044
 2-250 CU GRD PLT 2 HOLE
 Active

Web Use
 BURNDY Product Line

Length (in)
 Size (Hex) or Size (Bolt)
 Thickness
 D - in
 Pad Width (in)
 E - in

Dimensional

5.78
 1/2
 1.31
 3.25
 2.00
 1.75

Number of Holes (Tapped)
 Product Description
 Prefilled (Oxide Inhibitor)
 Copper Stranded (Range)

General

2
 Copper Compression Grounding
 Plate, 2 AWG - 250 kcmil, 1/2"
 Stud, 1-3/4" Stud Hole Spacing
 Y

Conductor(s)

2 AWG-250 kcmil

Physical

Type of Plating
 Plated (Yes or No)
 Index Number
 Product Material

Unplated
 N
 997
 Copper

Approvals / Certifications

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Y
 Y
 Y
 Exempt
 N
 N
 UL467,IEEE 837

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175