



BURNDY Catalog Number
UPC Number
Description
Status

YA6CL3BOX
 7818105530088
 6 STR CU 1-HOLE SHORT 5/
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.52
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.33
Barrel Type	Standard
Thickness	0.07
B Length (in)	0.54
Pad Width (in)	0.52
Strip Length	9/16

General

Number of Holes	1
Product Description	CU Compression Terminal Code Conductor, Beveled Entry, 1 Hole/W/InspWindow, #6AWG(Code), 600V-35kV, 5/16" Stud, Standard Barrel, Electro-Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	6 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	5/16
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7,374
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175