



BURNDY Catalog Number
UPC Number
Description
Status

YGHP29C26
7818102209311
1/0-250 TO 1/0-2/0 GRN C
Active

Web Use
BURNDY Product Line

B Length (in)
B Length (Fraction)

Dimensional
0.75
3/4

Product Description

General
Cu Compression Ground Rod
Connector, 1/0 Str - 2/0 str, 1/2" -
5/8" Rod Dia

Prefilled (Oxide Inhibitor)

Y

Type of Oxide Inhibitor

Other
Penetrox E

Rated for Direct Burial

Approvals / Certifications

UL Listed

Y

CSA Certified

Y

ROHS Compatible

Y

UL Recognized

Compliant

CULUS

N

Industry Standards

N

UL467,IEEE 837

Copper Tap Range

Conductor(s)
1/0 -2/0 AWG

Copper Stranded Run (Range)

1/0 -250 kcmil

Copper Solid Tap (Range)

N/A

Copper Solid Run Size (Range)

N/A

Type of Plating

Physical
Unplated

Connector Type

Tap

Plated (Yes or No)

N

Index Number

997

Product Material

Copper

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

BURNDY Technical Services

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175

47 East Industrial Park Drive
Manchester NH 03109

47 East Industrial Park Drive
Manchester NH 03109