



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA6CL1BOX  
 7818105528033  
 6 STR CU1HLE SHT8-GLOBAL  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Tongue Angle	Straight
Length (in)	1.27
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Barrel Type	Standard
Thickness	0.09
B Length (in)	0.54
Pad Width (in)	0.41
Strip Length	9/16

**General**

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 6 AWG, #8-#10 Stud, Short Barrel, Tin Plated

**Conductor(s)**

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	6 AWG

**Physical**

Type of Plating	Tin - Electro Plated
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7,374
Product Material	Copper

**Approvals / Certifications**

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175