



BURNDY Catalog Number
UPC Number
Description
Status

YAV10T2
 7818100252600
 12-10 HVYDTY RING 5/16 S
 Active

Web Use
 BURNDY Product Line

Length (in)
 Tongue Type
 Stud Size (in)
 Pad Width (in)

Dimensional

1.06
 Ring
 5/16
 0.53

General

Hylug, 12-10 AWG, 8-10 , .97 in L,
 .36 in W, Tin- Electro plated

Conductor(s)

Aircraft Cable Size (Range)
 Copper Solid Size (Range)
 Navy Cable Size (Range)
 Copper Stranded (Range)

N/A
 12 AWG-10 AWG
 N/A
 12 AWG-10 AWG

Physical

Type of Plating
 Connector Type
 Plated (Yes or No)

Tin - Electro Plated
 Terminal - Ring
 Y

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 Mil-Spec Class Code
 CULUS

Y
 Y
 Compliant
 N
 Class 1, Class 2
 N
 UL467, Military Specified (Mil-Spec)

Industry Standards

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175