



BURNDY Catalog Number YC8C8
UPC Number 7818101145066
Description 8 TO 10-8 CU FIG C
Status Active

Web Use
 BURNDY Product Line

Dimensional	
Length (Fraction)	1/2
General	
Product Description	CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, Run: 8 Sol. - 8 Str., Tap: 10 Sol. - 8 Str.
Conductor(s)	
Copper Tap Range	10 AWG-8 AWG
Copper Stranded Run (Range)	8 AWG
Copper Solid Tap (Range)	10 AWG-8 AWG
Copper Solid Run Size (Range)	8 AWG
Physical	
Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
Industry Standards	UL 486A,UL486B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175