



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YGHR26C34  
 7818102207266  
 2-2/0 TO 3/4 GRD ROD FIG  
 Active

**Web Use**  
 BURNDY Product Line

Length (in)  
 Height (in)  
 B Length (in)  
 B Length (Fraction)

**Dimensional**  
 0.88  
 2.19  
 0.88  
 22/25

Product Description

**General**  
 Copper Compression Connector, 2  
 AWG(Str)-2/0 AWG(Str), 3/4"  
 Ground Rod  
 Y

Prefilled (Oxide Inhibitor)

**Other**  
 Penetrox E

Type of Oxide Inhibitor

**Approvals / Certifications**

Rated for Direct Burial  
 UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS  
 Industry Standards

Y  
 Y  
 Y  
 Compliant  
 N  
 N  
 UL467,IEEE 837

Copper Stranded (Range)

**Conductor(s)**  
 2 AWG-2/0 AWG

Type of Plating  
 Connector Type  
 Plated (Yes or No)  
 Index Number  
 Product Material

**Physical**  
 Unplated  
 Tap  
 N  
 998,1012  
 Copper

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175