

Conductor marker carrier - PATG 2/12 - 0827078

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker carrier, transparent, unlabeled, mounting type: slide on, cable diameter range: 2 - 4 mm, lettering field size: 12 x 4 mm

Your advantages

- The corresponding UC-WMT ..., US-WMT ..., and EMT ... insert labels are used for marking
- The PATG ... collar is a captive marker carrier
- These conductor marking systems consist of marker carriers and insert labels
- Can be used to mark conductors with a diameter of 0.6 ... 50 mm

Key Commercial Data

Packing unit	1000 pc
Minimum order quantity	1000 pc
GTIN	
GTIN	4046356417174

Technical data

Dimensions

Length (b)	12 mm
Width (a)	5 mm
Cable diameter	2 mm ... 4 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
---------------------------------	------------------

General

Color	transparent
Type	Profile
Components	Silicone-free
Flammability rating according to UL 94	V0

Conductor marker carrier - PATG 2/12 - 0827078

Technical data

General

Material	PVC
RoHS compliant	Yes
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Marking mounting type	slide on
Min. cross section	2 mm ²
Max. cross section	4 mm ²

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>