

Articulating TV Wall Mount, VESA Wall Mount, Supports 26 to 65 inch/99lb/Flat/Curved TVs, Retractable Low Profile Wall Mount TV Bracket, Adjustable Corner TV Wall Mount

Product ID: TV-WALL-MOUNT-65FS



This VESA TV Wall Mount supports TV displays from 26" to 65" and up to 99.2 lb (45kg). Robust steel and aluminum frame for a long-lasting TV installation. The arm assembly provides smooth motion and retracts towards the wall for low-profile configurations. In addition, the articulating TV wall mount features an array of adjustments for an ideal viewing angle and supports VESA patterns from 200x200 to 400 x400.

Securely mount a flat or compatible curved-screen TV or digital signage for visitors, clients, and employees to view. This TV wall mount is ideal for lobbies, boardrooms, and manufacturing facilities.

The lateral range of 3.1ft (95.6cm) is ideal for corner mounting, and the jointed arm folds on itself, creating a slim profile from the wall of just 4.1in (10.5cm) for limited-space installations.

Mount the articulating TV wall mount to a single wood stud or a concrete wall using the included keyhole-style mounting plate for quick and hassle-free installation. In addition, M4/5/6/8 screws of various lengths, matching washers, and spacers enhance the TV mounting compatibility.

Supported VESA mounting patterns: 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, and 400x400.

Customize the viewing experience and comfort with these adjustment capabilities. The TV mount can rotate +90/-90 degrees at the wall mount assembly plate, as well as at both pivot points, while the VESA vertical bracket can be tilted +15/-15 degrees.

The arm assembly extends up to 22.1in (56.2cm) from the wall to accommodate different viewing positions, including corner mounting. Built-in cable management and a wall mount cover for an organized and visually appealing installation.

This TAA corner TV mount is backed for five years, including free lifetime 24/5 multi-lingual technical assistance.

### **Certifications, Reports and Compatibility**



## **Applications**

#### **Features**

- PREMIUM 65" TV WALL MOUNT: Articulating wall mount TV bracket supports TVs up to 65 inches; VESA patterns from 200x100 up to 400x400; Max weight capacity 99lb (45kg); Durable and sturdy frame with silver finish; For flat or curved screen TVs
- VERSATILE: Adjustable corner TV wall mount features tilt & swivel torque adjustment for smooth positioning; VESA wall mount features +/-90 swivel, +/-15 tilt, and double swivel arms; Low-profile TV mount allows for 4.13in from the wall and up to 22.1in
- EASY INSTALLATION: This extendable TV wall mount ships assembled for quick deployment; Articulating TV wall mount features integrated bubble level, mounting template, and wall plate with keyhole mounting for a swift installation
- COMPATIBILITY: Single stud TV mount for compatible TVs from Samsung, Sony, Hisense, TCL, and LG, among others; Compatible with most VESA patterns; Includes wood stud & concrete wall mounting hardware, spacers, adjustment tools, and various-sized screws
- AESTHETIC DESIGN: Robust steel and aluminum construction with decorative covers to maintain a professional look; Built-in cable management solution ideal for customer-facing applications; Retractable TV mount requires a single wood stud for installation

Hardware		
	Warranty	5 Years
	Wallmountable	Yes
	Cable Management	Yes
	Tools Included	Yes
	Articulating	Yes
	# of Displays Supported	1
	Orientation	Horizontal
	Mounting Options	Wall-Mount
	Minimum Profile from Wall	4.1 in [105 mm]
	VESA Hole Pattern(s)	200x100 mm





200x200 mm

200x300 mm

200x400 mm

300x200 mm

300x300 mm

400x200 mm

400x300 mm

400x400 mm

**Performance** 

General Specifications Minimum Distance to Wall: 4.1 in (10.5 cm)

Maximum Distance to Wall: 23.1 in (56.2 cm)

Weight Capacity (Per

Display)

99.2 lb [45 kg]

Minimum Display Size 26in

\_

Maximum Display Size

65"

Fits Curved Display

Yes

Fits UltraWide Displays

Yes

Video Wall

No

Height Adjustment

No

Minimum Arm Extension

4.1 in [105 mm]

Maximum Arm Extension

22.1 in [562 mm]

Display Tilt

+ 15 / - 15

Display Swivel

180

Display Rotation

+90 / - 90

Physical Characteristics

Color

Black & Silver





Construction Material Aluminum and Steel

Product Length 17.7 in [45.0 cm]

Product Width 19.7 in [50.0 cm]

Product Height 4.1 in [10.5 cm]

Weight of Product 17.1 lb [7.8 kg]

# Packaging Information

Package Quantity 1

Package Length 18.1 in [46.0 cm]

Package Width 24.6 in [62.4 cm]

Package Height 4.9 in [12.4 cm]

Shipping (Package)

Weight

20.4 lb [9.2 kg]

#### What's in the Box

Included in Package 1 - TV Wall-Mount Assembly

2 - Vertical Brackets

1 - 6 mm Hex Key

2 - Vertical Bracket Screws

8 - Concrete Anchors

8 - Wall Mounting Screws

4 - M4 x 12 mm Screws

4 - M4 x 18 mm Screws

4 - M5 x 12 mm Screws

4 - M6 x 12 mm Screws

4 - M6 x 18 mm Screws

4 - M8 x 12 mm Screws

4 - M8 x 18 mm Screws



- 4 Flat Washers
- 1 Mounting Template
- 1 User Manual

\*Product appearance and specifications are subject to change without notice.