

8			7			6		
PIN #	COLOR	AWG	PIN #	COLOR	AWG			
1	BLACK	24AWG	14	GREEN	24AWG			
2	BLACK/WHITE	24AWG	15	GREEN/BLACK	24AWG			
3	BROWN	24AWG	16	GREEN/WHITE	24AWG			
4	BROWN/WHITE	24AWG	17	BLUE	24AWG			
5	RED	24AWG	18	BLUE/WHITE	24AWG			
6	RED/BLACK	24AWG	19	VIOLET	24AWG			
7	RED/WHITE	24AWG	20	VIOLET/WHITE	24AWG			
8	ORANGE/BLACK	24AWG	21	GRAY	24AWG			
9	ORANGE	24AWG	22	GRAY/BLACK	20AWG			
10	ORANGE/WHITE	24AWG	23	PINK	20AWG			
11	YELLOW	24AWG	24	PINK/BLACK	20AWG			
12	YELLOW/BLACK	24AWG	25	WHITE	20AWG			
13	LIGHT GREEN	24AWG						

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/26/2012	BEM




TABLE A	
P/N	L
DB25-MFP-2M	2M [79"]
DB25-MFP-3M	3M [118"]
DB25-MFP-5M	5M [197"]
DB25-MFP-6M	6M [236"]
DB25-MFP-10M	10M [393"]
DB25-MFP-12M	12M [472"]

NOTES:  
CABLE: 24/21 & 20/4 SHIELDED CABLE WITH 20AWG DRAIN  
FULL LENGTH MYLAR FOIL SHIELD  
FULLY WIRED STRAIGHT THRU

SHIELD & 20 AWG DRAIN CONNECTED TO METAL SHELL

BRASS NICKEL PLATED THUMB SCREWS

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS  
DRAWING IS THE SOLE PROPERTY OF  
MENCOM CORPORATION. ANY  
REPRODUCTION IN PART OR AS A WHOLE  
WITHOUT THE WRITTEN PERMISSION OF  
MENCOM CORPORATION IS  
PROHIBITED.

		UNLESS OTHERWISE SPECIFIED:		NAME	MENCOM CORPORATION			
		DIMENSIONS ARE IN MM AND [INCHES]	DRAWN	CAM				
			CHECKED					
			ENG APPR.					
			MFG APPR.					
			Q.A.		TITLE: DB25 MALE/FEM EXT CABLE GUARANTEED COLOR CODE			
			COMMENTS:					
		MATERIAL				SIZE	DWG. NO.	REV
		FINISH				<b>B</b>	DB25-MFP-ZZ	<b>A</b>
		DO NOT SCALE DRAWING				SCALE: 1:1	WEIGHT:	SHEET 1 OF 1