


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/16/2022	DGUTTADAURO



WIRING CHART			
1	1	BROWN	POWER L +12V
14	14	1	INNER SHIELD
2	25	WHITE	Tx DATA 0-
15	12	RED	Tx DATA 0+
3	24	WHITE	Tx DATA 1-
16	11	BLUE	Tx DATA 1+
4	23	WHITE	Tx DATA 2-
17	10	GREEN	Tx DATA 2+
5	22	WHITE	XCLK-
18	9	YELLOW	XCLK+
6	21	WHITE	Tx DATA 3-
19	8	VIOLET	Tx DATA 3+
7	20	RED	SerTC+
20	7	BLACK	SerTC-
8	19	BLACK	SerTFG-
21	6	BLUE	SerTFG+
9	18	BLACK	CC1-
22	5	GREEN	CC1+
10	17	YELLOW	CC2+
23	4	BLACK	CC2-
11	16	BLACK	CC3-
24	3	VIOLET	CC3+
12	15	WHITE	CC4+
25	2	BLACK	CC4-
13	13	2	INNER SHIELD
26	26	ORANGE	POWER L +12V
		HOUSING	OUTER SHIELD



PART NUMBER	LENGTH	
	FEET	METERS
CLCA02-1M	3.28	1.0
CLCA02-3M	9.84	3.0
CLCA02-5M	16.4	5.0

NOTES:

1. CABLE SHALL BE TESTED FOR CONTINUITY.
2. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY DMAY	6/16/2022		
	CHECKED BY DFRISIELLO	6/17/2022	CATEGORY	AUDIO/VIDEO
	APPROVED BY DGUTTADAURO	6/17/2022	PRODUCT DESCRIPTION	
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	CAMERA LINK CABLE ASSEMBLY, MDR/SDR, PVC, IV	
	SIZE A	CAGE CODE 43321	ITEM NO. CLCA02	
	SCALE: NONE	CAD FILE: CLCA02.SLDDRW	SHEET 1 OF 1	