8	7	6	5	4	3		2		1	
PIN # COL	OR					REVISIONS				
					REV.	DESCRIPTIC		DATE	APPROVED	
1 BRC	WN				A	REDRAWN IN	1 SW	9/9/2010	BEM	
2 GRA										
3 BLA										
GND GRE	EN / YELLOW									
			ND FLAT GASKET SUPF CH CABLE	PLIED			TABLE A P/N		- STD?	
	16	WIIII EAC								
	.6			[6]			VCN-130-0	0 11	M NO	
		_		Ø.23			VCN-230-0	0 21	M YES	
.6		fr.					VCN-330-0	0 3	M NO	
				A			VCN-430-0	0 4	M NO	
							VCN-530-0	0 51	M YES	
	*		<b>CIRCUIT N</b>				VCN-630-0	0 6	M NO	
			$\leftarrow$	< 1						
MATERIALS				^			VCN-A30-0		M YES	
				2			Parts listed May requ	AS NOT BEINC JIRE MINIMUN	3 STANDARE 1 ORDERS	
BODY: CONTACTS:	BLACK POLYAMIDE SILVER PLATED COPPER ALLOY		<	< 3	UNLESS OTHERWISE SPECI	FIED: N/				
INSERT:	POLYAMIDE				DIMENSIONS ARE IN INCHES & [MM]	DRAWN C	AM MENCO			
CABLE:	BLACK PVC		<	GND	~ frand	CHECKED ENG APPR.	TITLE:			
GASKET:		-	AC/DC 250V			MFG APPR. DIN C W/O ELECT 3+E				
SCREW:	ZINC PLATED STEEL		3 POLES + GND	PROPRIETARY AND CONFIDENTIAL		Q.A. COMMENTS:				
WIRE:	4X20AWG; CABLE OD 0.23"			THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MENCOM CORPORATION. ANY	MATERIAL	COMMETTS.	SIZE DWG. NO		RE	
TEMP:	-40°C TO +80°C (-40°F TO +176°F)			REPRODUCTION IN PART OR AS A WHOLI WITHOUT THE WRITTEN PERMISSION OF	FINISH		<b>B</b> v	CN-ZZ30-00	A	
				MENCOM CORPORATION IS						

	NAME	MENCOM CORPORATION								
	CAM									
		TITLE:								
					2 I F		A			
			DINC	C W/O ELECT	3+E					
		SIZE D'	NG. NO.			REV				
		В	VCN	1-ZZ30-00	Α					
					0					
SCALE: 2:1		I WEIGHI:	WEIGHT:		[ 1 OF 1					
		2			1					