

Classical Cogged V-Belt

Goodyear Belts has developed Classic Cogged V-belts that offer premium performance, ensuring a long service life. Restore your belt drive system's efficiency by installing a new Goodyear Belt.

- Static Conductive
- Meets or Exceeds OEM Specifications
- Long-life EPDM Rubber Compound– Operating Temperature from -31F to 248F (-31C° to 120C°)
- Proprietary rubber formulation for quiet operation
- Radial cog design increases efficiency and reduces cracking
- Precision ground sides for maximum pulley contact
- Synthetic tensioner members ensuring excellent tensile strength
- Limited 1-Year Warranty



Belt Material:	EPDM	Belt Type:	Classic
Construction:	Cogged	Cord Material:	Polyester
Effective Length (in):	50.98	Effective Length (mm):	1295
Item Weight (kg):	0.1	Item Weight (lbs):	0.22
Outside Circumference (in):	51.35	Outside Circumference (mm):	1304
Profile:	AX	Rib Angle:	36°
Thickness (in):	0.315	Thickness (mm):	8
Top Width (in):	0.512	Top Width (mm):	13