

Narrow Cogged V-Belt

Goodyear Belts has developed Narrow Cogged V-Belts that offer premium performance, ensuring a long service life. Restore your belt drive system's efficiency by installing a new Goodyear Belt.

- Meets or Exceeds OEM Specifications
- Long-life EPDM Rubber Compound
- Proprietary rubber formulation for quiet operation
- Radial cog design increases efficiency and reduces cracking
- Precision ground ribs for maximum pulley contact
- Tie-Band construction High strength tensile cords designed for minimal tension decay and low maintenance
- Limited 1-Year Warranty



Belt Material:	EPDM	Belt Type:	Narrow
Construction:	Cogged	Cord Material:	Polyester
Effective Length (in):	85	Effective Length (mm):	2159
Item Weight (kg):	0.44	Item Weight (lbs):	0.97
Outside Circumference (in):	85.49	Outside Circumference (mm):	2172
Profile:	5VX	Rib Angle:	38°
Thickness (in):	0.52	Thickness (mm):	13.2
Top Width (in):	0.622	Top Width (mm):	15.8

Interchanges

Interchange is provided as a reference. Please check part specifications to verify fit.

Reference Number	Reference Name
2020B40H61	Thermo-King
2L437	Dayton Parts
5VX850	AC Delco
5VX850	Continental
5VX850	Gates
78283	Thermo-King