



Siemens Low Voltage Circuit Protection OEM Disconnect & Accessories. Type: OEM DISCONNECT SWITCH Std: UL V. Rating: 600VAC A. Rating: 30 A No. Of Poles: 3P F. Rating: 60Hz Action: SINGLE THROW. O. Cycles: 10000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: INDOOR

General technical data	
fastening method	Panel Mounting
Electricity	
voltage between phase and phase rated value	60000000 V
Model	
product brand name	Siemens
product type designation	OEM Disconnect Switch
General product approval	
certificate of suitability	UL/CSA

last modified:

8/1/2022

