



**Product #:** 8561830

**Order Symbol:** AR IPW 1210 W F

**Description:** Protection Window - HMI Cover

**Remarks:** Opaque flat cover with non locking wing knobs.

| Dimensions | Length | Width | Height |
|------------|--------|-------|--------|
| Inch       | 3.31   | 10    | 12     |
| mm         | 88     | 295   | 342    |

| Materials        |                      |
|------------------|----------------------|
| Material:        | Polycarbonate        |
| Base color:      | RAL 7035 -light grey |
| Cover color:     | RAL 7035 -light grey |
| Gasket material: | Polyurethane         |

| Temperatures                 |             |
|------------------------------|-------------|
| Temperature °F (short term): | -40 ... 250 |
| Temperature °F (continuous): | -40 ... 175 |
| Temperature °C (short term): | -40 ... 140 |
| Temperature °C (continuous): | -40 ... 80  |

| Ratings                                |                                   |
|----------------------------------------|-----------------------------------|
| Ingress Protection (EN 60529):         | IP66; IP67;                       |
| Impact Resistance (EN 62262):          | IK09;                             |
| Halogen free (DIN/VDE 0472, Part 815): | Yes                               |
| UV resistance:                         | UL 508                            |
| Flammability Rating:                   | UL94-5VA (f1)                     |
| Glow Wire Test (IEC 60695):            | 960 °C                            |
| UL/cUL Type:                           | NEMA 4, 4X, 6, 6P, 12, 12K and 13 |