




WGO terminal block label



Product information

WGO - for terminal manufacturers Wago, Beckhoff and ABB Entelec. High-quality, halogen-free snap-in label plates. Labels available for mounting individually or in strips.

The large printable area at the top allows room for individual project and terminal block reference, dispensing with the need for additional organisational systems.

Information, conformities and approvals



Article	Order No.	Color	RAL equiv.	Label size * mm	Printable	Number of characters / lines	Quantity per frame	Base plate	Software Article	PU pcs.
4-4.2 mm grid strips in a row, with contoured foot										
WGO 3.4/10-4...4.2 F	86401806	White	9016	3.4 x 10	3.4 x 10	5 / 1	100	GP4	499	1300
4 mm pitch strips in a row, with contoured foot										
WGO 4/10-4 F	86401808	White	9016	4 x 10	4 x 10	5 / 1	100	GP4	162	1300
5.1 mm-grid strips in a row, (long mat version)										
WGO 5/5-5.1 L	86401870	White	9016	5 x 5	5 x 5	2 / 1	100	GP5	541	1100
WGO 5/5-5.1 L	86401872	Yellow	1018	5 x 5	5 x 5	2 / 1	100	GP5	542	1100
WGO 5/5-5.1 L	86401876	Green	6018	5 x 5	5 x 5	2 / 1	100	GP5	546	1100
WGO 5/5-5.1 L	86401874	Red	2012	5 x 5	5 x 5	2 / 1	100	GP5	544	1100
WGO 5/5-5.1 L	86401878	Blue	5012	5 x 5	5 x 5	2 / 1	100	GP5	543	1100
WGO 5/5-5.1 L	86401873	Orange	2011	5 x 5	5 x 5	2 / 1	100	GP5	545	1100
5 mm pitch strips in a row										



WGO terminal block label

Article	Order No.	Color	RAL equiv.	Label size * mm	Printable	Number of characters / lines	Quantity per frame	Base plate	Software Article	PU pcs.
WGO 5/10-5	86401810	White	9016	5 x 10	5 x 10	5 / 1	88	GP4	49	2000
5 mm pitch strips in a row, with contoured foot										
WGO 5/10-5 F	86401813	White	9016	5 x 10	5 x 10	5 / 1	88	GP4	139	1400
5 mm pitch strips in a row (can be applied to a 6 mm pitch pattern)										
WGO 5/10-5...6 F	86401812	White	9016	5 x 10	5 x 10	5 / 1	88	GP4	141	1400
6.2 mm pitch strips in a row (can be applied to a 7.5 mm pitch pattern)										
WGO 5.2/10-6.2...7.5 F	86401850	White	9016	5.2 x 10	5.2 x 10	5 / 1	68	GP4	540	1088

Material properties



Polycarbonate (PC)

Thermal properties



Temperature / temperature range -40 °C – 130 °C

Fire properties



Fire classification V0

Technical information



Halogen-free

General technical data



Individual and strip mounting



WGO terminal block label

Assembly method



Snap-fit system



Strip system

Labelling technology



Plotter



Laser devices



Inkjet